



1010 Cambourne Business Park: Cambridge: CB23 6DP: Tel +44 1223 923930: Fax +44 1223 923940

Information Sheet

Dear Sirs,

Thank you for purchasing this Hokuyo UTM-30LX product.

On this enclosed CD you will find copies of the Data Sheet, the Technical Specifications, the SCIP2.0 Communication Protocol and finally a ZIP file with a display application VMON 0804. There are also details of some of the other laser scanners produced by Hokuyo.

Please note the following points:

- a) The SCIP2.0 document makes reference to the URG-04LX product which has different range and scanning angle characteristics to the UTM-30LX. However the data encoding & decoding method along with the commands are valid for the UTM-30LX. This means any existing SCIP2.0 compatible programs you have developed for the URG-04LX can be used directly with the UTM-30LX.
- b) The firmware installed in the UTM-30LX is only valid for use with SCIP2.0.
- c) Do not disconnect the USB from the PC without first closing the VMON application.
- d) In use the housing temperature of the UTM-30LX becomes quite warm. This is normal but we recommend that it is mounted on a metal plate to sink some of the generated heat.
- e) Hint – when you have the VMON display on screen “right click” to view settings.

We trust you will be satisfied with this unique laser scanner. Please feel free to contact us in case of query.

Yours sincerely

Sentek Solutions.

Authorised European Distributor

for Hokuyo Automatic Japan



ISO 9001 Certified JQA 1742